

Decorator Slide Fan Control, Preset/3-Speed/5A



## Features & Benefits

Tough impact-resistant thermoplastic housing.

Power-failure memory.

Superior heat management: no time wasting break off tabs.

Exclusive screw-pressure-plate back wire terminals eliminates wire nuts.

Can be used with patented Snap-In Light Module (sold separately).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007158113
Country Of Origin	China	Features	Variable Speed Fan Control
Switch Type	Rocker, Slider	Number of Switches	1
Application Sector	Multi-Dwelling Unit, Residential	Standard	UL Listed
Warranty Type	Limited Lifetime Warranty	Type	Fan Speed Control

### Dimensions

Product Width US	1.74 in	Product Depth US	1.28 in
Product Height US	4.185 in		

Listing Agencies / 3rd Party Agencies

cULus Listed                      Yes

Technical Information

Preset                      Yes                      Load Rating                      120V 5A (Fan Control)

Operating Cycles                      100000                      Dimming Compatibility                      Fan Speed Only

Frequency Rating                      60 Hz                      Number of Poles                      Single Pole

Wire Size                      #14 - #12 AWG                      Requires Neutral Wire                      No

Indoor/Outdoor                      Indoor                      Mounting Type                      Wall Box

Wire Connection Type                      Screw Terminals                      Voltage                      120 VAC

Load Type                      AC Fan Motor