



C2G
UPS, Online, LCD, 1500VA, 120V, 2U, (8) 5-15R, 5-15P Cord
Part No. LU-1500-RT



Protect mission critical hardware in IT closets, voice and data networks, unmanned facilities, light industrial, and financial branches through double-conversion online power protection. Multiply the reach and ability of IT staff and caretakers through a single portal, providing visibility and control of power usage and available capacity, simplifying maintenance responsibilities for taxed IT departments.

Features & Benefits

- Zero Transfer Time:** Seamless transfer of power from AC to battery and inverter to bypass
- Pure Sinewave Output:** Provides the ideal waveform for the most sensitive equipment
- Input Power Factor Correction:** Optimized and ideal efficiency at full load
- Designed to Work in Tandem with a Generator:** Ensures smooth transition to generators during longer outages
- 4-Post Rack Mounting Kit:** Included for simplified rack mounting
- True Double-Conversion:** Provides the highest protection from raw input power (surges, spikes, and dips)
- Wide Input Voltage Range:** Enables stable wide range application usage
- Programmable Outlet Bank:** Ensures efficient and timely powering down of attached non-critical equipment
- Optional Remote Management Control:** Provides visibility and control of power usage and availability, both on-site or at a remote unmanned facility
- Tower Mounting Option:** Includes feet for non-rack applications, enabling the UPS to stand up by providing stability

Specifications

General Info

| | | | |
|--------------------|--------------|-------------------|------------------------------------|
| Product Line | TBD | Color | Black |
| UPC Number | 662875017042 | Country Of Origin | China |
| Application Sector | Commercial | Standard | UL 1782 |
| Warranty Type | 2-Year | Type | UPS (Uninterruptible Power Supply) |

Technical Information

| | | | |
|------------|-----|-----------|-------|
| Rack Units | 2 U | Plug Type | 5-15P |
|------------|-----|-----------|-------|

Wattage

1500 W

Mounting

Horizontal

Number of Outlets

8

Voltage

120.0 V
