



Momentum 2 modular fiber optic pre-terminated cassettes provide the fastest method of structured cabling deployment: plug it in and you're ready to go. Factory-terminated and tested cassettes guarantee field performance.

Features & Benefits

Compact, pre-terminated modular system: Provides quick and easy deployment, Common cassette mounting footprint: Fits in all Ortronics moves, adds and changes, eliminating costly field installation time. rack mount cabinets and raised floor patch panels.

Data label printed with insertion loss value for each port adhered to the cassette housing. Available in Single, Multi-Mode, 12 fiber or 24 fiber ports

Specifications

General Info

Product Line	Ortronics	UPC Number	662875609315
Country Of Origin	Taiwan, Province Of China	Application Sector	Commercial
Standard	TIA-568-C.3	Warranty Type	5-Year
Type	Cassette		

Dimensions

Product Width US	5.13 in	Product Depth US	5.42 in
Product Height US	1.19 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Fiber Optic Cable Type	OS2	Rack Units	1
Number of Ports	12	Simplex/Duplex	Duplex
Single/Multimode	Single-Mode		