

Ortronics 12-FIBER OM4+ M4 CASSETTE WITH 12 LC DUPLEX ADAPTERS TO 1 MPO M-TIER 3- METHOD B- FAR END

Part No. M4LCD12-50EC3B1



Infinium M4 pre-terminated cassettes with method B provide rapid deployment and have a flipped polarity inside the modules, which use key-up to key-up MPO adapters and allows for straight through patching. The rugged metal housing offers additional durability and includes a built-in internal bend limiting feature to assure optimum optical performance.

Features & Benefits

Fully Compatible with Infinium INFC Enclosures			4 Cassettes Fit into 1U	
ront Adapter Housing Colors Follow TIA/EIA-568.3-D Suggested Color Identification Scheme			Each cassette has a data label with insertion loss value for each port	
Specifications				
General Info				
Product Line	Ortronics	UPC Num	ber	662875001263
Country Of Origin	United States	Applicatio	n Sector	Commercial
Standard	TIA-568-C.3	Туре		Cassette
Dimensions				
Product Width US	3.45 in	Product C	epth US	4.77 in
Product Height US	1.14 in			
Additional Information				

RoHS Conformant

Yes