



Ortronics
12-FIBER OM4+ M4 CASSETTE WITH 12 LC DUPLEX ADAPTERS TO 1 MPO M- TIER 3- METHOD B- FAR END
Part No. M4LCD12-50EC3B1

Infinium M4 pre-terminated cassettes with method B provide rapid deployment and have a flipped polarity inside the modules, which use key-up to key-up MPO adapters and allows for straight through patching. The rugged metal housing offers additional durability and includes a built-in internal bend limiting feature to assure optimum optical performance.



Features & Benefits

Fully Compatible with Infinium INFC Enclosures	4 Cassettes Fit into 1U
Front Adapter Housing Colors Follow TIA/EIA-568.3-D Suggested Color Identification Scheme	Each cassette has a data label with insertion loss value for each port

Specifications

General Info

Product Line	Ortronics	UPC Number	662875001263
Country Of Origin	United States	Application Sector	Commercial
Standard	TIA-568-C.3	Type	Cassette

Dimensions

Product Width US	3.45 in	Product Depth US	4.77 in
Product Height US	1.14 in		

Additional Information

RoHS Conformant	Yes
-----------------	-----