



Infinium M4 pre-terminated cassettes with method B provide rapid deployment and have a flipped polarity inside the modules, which use key-up to key-up MPO adapters and allows for straight through patching. The rugged metal housing offers additional durability and includes a built-in internal bend limiting feature to assure optimum optical performance.

## Features & Benefits

- High Density: 12 or 24-fiber cassette compatible with Infinium HD M4 Enclosures :
- Versatile Installation: Infinium Modular Panel enables mixed media installations
- Fiber Type: Supports either Single-mode OS2 or Multimode Infinium Ultra fiber
- Insertion loss value for each port printed on adhesive data label

## Specifications

### General Info

Product Line	Ortronics	UPC Number	662875001287
Country Of Origin	China	Application Sector	Commercial
Standard	TIA-568-C.3	Type	Cassette

### Dimensions

Product Width US	3.45 in	Product Depth US	4.77 in
Product Height US	1.14 in		

### Additional Information

RoHS Conformant	Yes
-----------------	-----