



Infinium M4 pre-terminated cassettes with method B provide rapid deployment and have a flipped polarity inside the modules, which use key-up to key-up MPO adapters and allows for straight through patching. The rugged metal housing offers additional durability and includes a built-in internal bend limiting feature to assure optimum optical performance.

Features & Benefits

High Density: 12 or 24-fiber cassette compatible with Infinium HD M4 Enclosures :	Versatile Installation: Infinium Modular Panel enables mixed media installations
Fiber Type: Supports either Single-mode OS2 or Multimode Infinium Ultra fiber	Insertion loss value for each port printed on adhesive data label

Specifications

General Info			
Product Line	Ortronics	UPC Number	662875001287
Country Of Origin	China	Application Sector	Commercial
Standard	TIA-568-C.3	Type	Cassette
Dimensions			
Product Width US	3.45 in	Product Depth US	4.77 in
Product Height US	1.14 in		
Additional Information			
RoHS Conformant	Yes		