



The 24-fiber OM4 M4 Cassettes are designed to be used with the Infinium HD Enclosures and support MPO to LC Quad adapter 24-fiber connectivity, with angle polished connectors delivering lower insertion loss, offering versatile installation and swift deployment. The housing of the cassettes offer additional durability and integrated bend limiting considerations to assure optimum optical performance.

Features & Benefits

- High Density: 12 or 24-fiber cassette compatible with Infinium HD M4 Enclosures
- Versatile Installation: Infinium Modular Panel enables mixed media installations
- Fiber Type: Supports either Single-mode OS2 or Multimode Infinium Ultra fiber

Specifications

General Info

| | | | |
|--------------------|--------------|-------------------|-------------|
| Product Line | Ortronics | Color | Aqua |
| UPC Number | 662875026198 | Country Of Origin | China |
| Application Sector | Commercial | Standard | TIA-568-C.3 |
| Warranty Type | 5-Year | Type | Cassette |

Dimensions

| | |
|------------------|---------|
| Product Width US | 4.24 in |
|------------------|---------|

Additional Information

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Technical Information

| | | | |
|------------------------|-----|------------------|--------------|
| Fiber Optic Cable Type | OM4 | Compatibility | Infinium, M4 |
| Number of Ports | 24 | Single/Multimode | Multimode |