



Ortronics  
Infinium M4 Cassette with 6 MPO MTO 2 24 Fiber MPO MTIER 4 - Universal Non-Flipped Polarity - OM4 - APC - Aqua  
Part No. M4MAE48-50EB4K1



The 24-fiber OM4 M4 Cassettes are designed to be used with the Infinium HD Enclosures and support MPO to MPO adapter 24-fiber connectivity, with angle polished connectors delivering lower insertion loss, offering versatile installation and simple deployment. The housing of the cassettes offer additional durability and integrated bend limiting considerations to assure optimum optical performance.

Features & Benefits

Multiple MTP to MTP breakout options to chose from	High Density, compatible with Infinium HD
Fiber Port Labeling provides easy administration	Supports MPO 12 and MPO 24 fiber applications

Specifications

General Info			
Product Line	Ortronics	Color	Aqua
UPC Number	662875025658	Country Of Origin	China
Application Sector	Commercial	Standard	TIA-568-C.3
Warranty Type	5-Year	Type	Cassette
Dimensions			
Product Width US	4.24 in	Product Depth US	3.21 in
Product Height US	1.23 in		
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Fiber Optic Cable Type	OM4	Compatibility	Infinium, M4
Number of Ports	48	Single/Multimode	Multimode
Performance Level/Tier	Infinium Quantum		