



Ortronics  
Infinium M4 Cassette with 6 MPO FTO 4 12 Fiber MPO MTier 4 - Universal Non-Flipped Polarity - OM5 - APC - Lin  
Part No. M4MBE48-50WA4K1



The 24-fiber OM4 M4 Cassettes are designed to be used with the Infinium HD Enclosures and support MPO to MPO adapter 24-fiber connectivity, with angle polished connectors delivering lower insertion loss, offering versatile installation and swift deployment. The housing of the cassettes offer additional durability and integrated bend limiting considerations to assure optimum optical performance.

Features & Benefits

Multiple MTP to MTP breakout options to chose from	High Density, compatible with Infinium HD
Fiber Port Labeling provides easy administration	Supports MPO 12 and MPO 24 fiber applications

Specifications

General Info			
Product Line	Ortronics	Color	White
UPC Number	662875025627	Country Of Origin	China
Included	Cover	Application Sector	Commercial, Data Center
Standard	TIA-568-C.3	Warranty Type	5-Year
Type	Cassette		
Dimensions			
Product Width US	4.24 in	Product Depth US	3.21 in
Product Height US	1.23 in		
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Fiber Optic Cable Type	OM5	Operating Temperature Min	-10 °C
Compatibility	Infinium, M4	Number of Ports	48
Operating Temperature Max	60 °C	Single/Multimode	Multimode
Performance Level/Tier	Quantum	Operating Temperature	-10°-60°C
Operating Humidity	0-80% RH (Non-Condensing)		