



Infinium M4 SC Splice Cassettes enable industry leading performance, fast field termination, and provide cable management within the housing. The Splice Cassettes are designed for use with Single-Mode (OS2) or Multimode (OM4/OM5) Fiber, Houses 12-24. Compatible with Infinium HD-E Rack Mount Fiber Enclosure with M4 Drawer Face.

Features & Benefits

- Mounts from either the front or rear of the enclosure or panel
- Tier 1 performance characteristics for insertion and return loss

Specifications

General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875027157	Country Of Origin	China
Application Sector	Commercial	Warranty Type	5-Year
Type	Cassette		

Dimensions

Product Width US	4.19 in	Product Depth US	6.15 in
Product Height US	1.24 in		

Technical Information

Fiber Optic Cable Type	OS2	Compatibility	M4
Number of Ports	12	Simplex/Duplex	Duplex
Return Loss	65 dB	Single/Multimode	Single-Mode
Performance Level/Tier	Infinium Core		