



Infinium M4 SC Splice Cassettes enable industry leading performance, fast field termination, and provide cable management within the housing. The Splice Cassettes are designed for use with Single-Mode [OS2] or Multimode [OM4/OM5] Fiber, Houses 12-24. Compatible with Infinium HD-E Rack Mount Fiber Enclosure with M4 Drawer Face.

## Features & Benefits

Mounts from either the front or rear of the enclosure or panel

Tier 1 performance characteristics for insertion and return loss

## Specifications

### General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875027164	Country Of Origin	China
Application Sector	Commercial	Warranty Type	5-Year
Type	Cassette		

### Dimensions

Product Width US	4.19 in	Product Depth US	6.15 in
Product Height US	1.24 in		

### Technical Information

Fiber Optic Cable Type	OS2	Compatibility	M4
Number of Ports	12	Simplex/Duplex	Duplex
Return Loss	55 dB	Single/Multimode	Single-Mode
Performance Level/Tier	Infinium Core	Maximum Insertion Loss	0.3 dB