



Ortronics
Clarity CAT6 Modular Patch Cord, 10 ft, White
Part No. MC610-09



Clarity® patch cords utilize center tuned technology to elevate channel performance. Clarity 6A, 6 and 5E cords are ETL verified to Category 6 and 5e component standards. More importantly, center tuning these cords to Clarity jacks and panels provides significant elevation of channel performance that can be field measured.

Features & Benefits

Center tuned to Clarity jacks and panels for a more transparent mated union
Narrow Paralign plug profile supports use in high density panels and hubs

Paralign™ 2 plug termination better controls plug performance

Icon compatible – provides additional TIA-606-A designation capabilities

Assembled with premium cordage, 100% factory tested for performance, reliability and long life

Specifications

General Info

Product Line	Ortronics	Color	White
UPC Number	662875458203	Country Of Origin	Mexico
Features	Standard Diameter	Application Sector	Commercial, Industrial
Standard	ANSI/TIA-568.E-2;ISO/IEC 11801-1;RoHS	Warranty Type	5-Year
Type	Copper Patch Cord		

Dimensions

Product Length US	10.0 FT	Cable Length	10 ft
-------------------	---------	--------------	-------

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
Technical Information			
Jacket Material	PVC	Operating Temperature Min	-10 °C
Category Performance Rating	Cat6	Compatibility	RJ-45
Wire Gauge	24 AWG	Storage Humidity	0-90% RH (Non-Condensing)
Plating Specification	50 µ in Gold	Jacket Application	Riser Rated
Bend Radius	0.88 in	Shielded/Unshielded	Unshielded
Termination Style	Pre-Terminated	Conductor Stranding	Stranded
Operating Temperature Max	60 °C	Cable Type	Non-Booted
Jacket Rating	CM Rated	Cable Diameter	0.22 in
Braid	Non-braided Wiring	Connector 2	RJ-45 Male
Connector 1	RJ-45 Male	Operating Temperature	-10°-60°C
Operating Humidity	0-90% RH (Non-Condensing)	Conductor Material	Copper
Voltage	300.0 V	Storage Temperature	-40° - 60° C