




Ortronics
MM20 Channel Rack, 10.5" deep, 7 ft, 45 RU, tapped, White
Part No. MM20710-W



Mighty Mo 20 channel racks are designed to provide greater flexibility and optimum efficiency to any size network. The top trough with built-in waterfall provides bend radius control and efficient patch cable routing. Honeycomb side rails on all depth channel racks provide the ultimate in distribution cable management. The honeycomb side rails, combined with airflow baffles, create a patented system that manages intake and exhaust air from side-vented equipment.

Features & Benefits

Many option for all applications: 5 depths, square hole or tapped hole configurations

Choice of vertical management: A solution for every application- vertical cable management cage with individual rack unit fingers and hinged slam latch door, vertical cage with individual rack unit fingers and snap on covers, vertical cage with hinged latches, and individual cable management rings.

Built-in top trough with waterfalls: Gives bend radius control and cable routing.

Can be assembled as a 19" or 23" rack: No additional hardware required- no need to stock two sizes of racks.

Speed nuts included: Increases speed and ease of assembly, while adding extra strength to your rack--Speednut eliminates the need for a second wrench.

Easy Installation: Mighty Mo 20 Racks can assemble in less than 15 minutes/rack

Large range of accessories

Cablofil® ready cable tray & runway brackets

Rack includes hardware kit, two packages of hook and loop D-style straps and 50 #12-24 equipment mounting screws: Do not have to purchase as separate items- money saving.

Honeycomb side rails designed to maximize the airflow of network equipment: Combined with baffles, manages intake and exhaust air creating cold aisle/hot aisle distribution from side vented equipment.

Open channels top and bottom: Allows floor and ceiling access for horizontal distribution cables.

Specifications

General Info

Product Line	Ortronics	UPC Number	662875216452
Country Of Origin	United States	Standard	UL 2416
Type	Rack		

Dimensions

Product Width US	23.75 in	Product Weight US	36.07 lb
Product Depth US	10.5 in	Product Height US	86.0 in

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Rack Units	45	Static Load Capacity	2000 lb
------------	----	----------------------	---------