



Mighty Mo 20 4-post racks fixed racks provide an economical mounting platform for switches and servers. Front and rear waterfalls allow for equipment patching and server patching. All styles of Mighty Mo 20 vertical managers can be mounted front or rear and airflow baffles can be mounted to manage the airflow of side breathing equipment.

Features & Benefits

Patented channel construction: Protects the performance of your horizontal cabling better than any other type of racking solution. Hex pattern on all rack sizes simplify cable routing.

Open channels top and bottom: Allows floor and ceiling access for horizontal distribution cables.

Choice of vertical management: A solution for every application- vertical cable management cage with individual rack unit fingers and hinged slam latch door, vertical cage with individual rack unit fingers and snap on covers, vertical cage with hinged latches, and individual cable management rings.

Can be assembled as a 19" or 23" rack: No additional hardware required- no need to stock two sizes of racks.

Rack includes hardware kit, two packages of hook and loop D-style straps and 50 #12-24 equipment mounting screws: Do not have to purchase as separate items- money saving.

Honeycomb side rails designed to maximize the airflow of network equipment: Combined with baffles, manages intake and exhaust air creating cold aisle/hot aisle distribution from side vented equipment.

High density racking solution

Built-in top trough with waterfalls: Gives bend radius control and cable routing.

Speed nuts included: Increases speed and ease of assembly, while adding extra strength to your rack--Speednut eliminates the need for a second wrench.

Specifications

General Info

Product Line	Ortronics	Color	Black
UPC Number	662875214830	Country Of Origin	United States
Application Sector	Commercial	Type	Rack

Additional Information

RoHS Conformant

Yes

Product Environmental Profile

Yes
