




## Ortronics

**Mighty Mo 20 Adjustable 4-Post Rack, 36"D adjustable, 7'H, 45 RU, Tapped Rails, White**  
Part No. MM20736ADJ12-W



Mighty Mo 20 4-post adjustable racks allow all 4 mounting rails to be adjusted even after the rack has been fastened to the floor. Available in depths of 30", 36" & 42" depths in both square hole cage nut styles or threaded rails. Front and rear waterfalls allow for equipment patching and server patching. All styles of Mighty Mo 20 vertical managers can be mounted front or rear and airflow baffles can be mounted to manage the airflow of side breathing equipment.

## Features & Benefits

Large selection of Channel and 4-Post racks

All 4 mounting rails to be adjusted even after the rack has been fastened to the floor

Front and rear waterfalls allow for equipment patching and server patching

Static capacity 2,000 lbs

Threaded hole and square hole punch available on all channel and 4 post racks

Deeper waterfall for increased cable capacity

Rack includes two packages of hook and loop D-style straps and 50 #12-24 cage nuts and screws, do not have to purchase as separate items; money saving

## Specifications

### General Info

Product Line	Ortronics	Color	White
UPC Number	662875216537	Country Of Origin	United States
Application Sector	Commercial	Type	Rack

### Dimensions

Product Width US	23.75 in	Product Weight US	56.28 lb
Product Depth US	46.0 in	Product Height US	86.0 in

### Additional Information

RoHS Conformant	Yes	Product Environmental Profile	Yes
-----------------	-----	-------------------------------	-----

---

## Technical Information

---

Static Load Capacity	2000 lb
----------------------	---------

---