



Mighty Mo 20 airflow baffles mount between racks, direct intake and exhaust air on side flow network equipment from cold aisle to hot aisle. The patented angle design utilizes less space, reduces back pressure and provides better overall performance than square duct style systems

### Features & Benefits

- Full height angled design: Provides increased intake area over square duct designs and reduces back pressure on the exhaust side of the switch.
- Manufactured from recycled PVC/ABS resin: Chemical and corrosion resistant, low flammability (UL-94 V0 flame rating), perfect for data center use.
- Lightweight foam core construction: Much easier to install, thermal and sound insulation (absorbs vibrations and oscillations) and reduced shipping cost and possibility of damage

### Specifications

#### General Info

Product Line	Ortronics	Color	Black
UPC Number	662875208419	Country Of Origin	United States
Application Sector	Commercial	Type	Rack

#### Dimensions

Product Width US	38.0 in	Product Depth US	0.125 in
Product Height US	41.47 in		

#### Additional Information

RoHS Conformant	Yes
-----------------	-----