



Add the convenience of a little extra light, wherever your home needs it, with this combination switch and built-in night light from the radiant® Collection. Easily replacing an existing single-pole or 3-way switch, the night light portion has five adjustable light levels and uses a hidden sensor to turn on when it is dark, making it a great addition to bathrooms, kitchens and nurseries. Features the sleek, clean lines of radiant for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

| | |
|--|--|
| Replaces any single-pole or 3-way switch with ease, in as little as 10 minutes. Offers installation flexibility, working in both single-pole and 3-way applications. | Features five adjustable light settings: Ultra Low, Low, Medium, High and OFF. |
| Hidden sensor controls night light based on ambient light, automatically turning on when it is dark. | Features durable, high-impact resistant thermoplastic construction. |
| More color options available to fit any style, including finishes to match current hardware and lighting trends. | Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection. |

Specifications

General Info

| | | | |
|--------------------|-------------------------|--------------------|------------------|
| Product Line | Pass & Seymour | Color | Nickel |
| Country Of Origin | China | Features | Nightlight |
| Switch Type | Push | Number of Switches | 1 |
| Application Sector | Residential | Standard | cULus, UL Listed |
| Warranty Type | 1-Year Limited Warranty | Type | Nightlight |

Dimensions

| | | | |
|-------------------|---------|------------------|--------|
| Product Width US | 1.29 in | Product Depth US | 1.3 in |
| Product Height US | 4.2 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|---------|--------------|-----|
| cULus ListingNumber | E140597 | cULus Listed | Yes |
|---------------------|---------|--------------|-----|

Technical Information

| | | | |
|-----------------------|-----|------------------|-------|
| Contact Configuration | 15A | Operating Cycles | 50000 |
|-----------------------|-----|------------------|-------|

| | | | |
|----------------|-----|-----------------|---|
| Contact Rating | 120 | Number of Gangs | 1 |
|----------------|-----|-----------------|---|

| | | | |
|----------|------|-----------------|--------------------|
| Amperage | 15 A | Number of Poles | 3-Way, Single Pole |
|----------|------|-----------------|--------------------|

| | | | |
|---------------|-----|---------|---------|
| Mounting Type | Box | Voltage | 120.0 V |
|---------------|-----|---------|---------|

| | | | |
|--------------------------|---------|--|--|
| Environmental Conditions | UL94 V2 | | |
|--------------------------|---------|--|--|