




## radiant Collection

radiant® 15A Tamper-Resistant Outlet with Night Light  
Part No. NTL885TRBKCC6



Perfect for adding a little light just where you need it, without sacrificing an outlet or dealing with unattractive plug-in models, this built-in night light from the radiant® Collection comes combined with a tamper-resistant outlet. A great upgrade for hallways and kids' bedrooms, it installs easily in place of a standard outlet and automatically comes on in the dark. With five adjustable light levels, you can easily set its brightness to meet your preferences or needs. Features the sleek, clean lines of radiant for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

### Features & Benefits

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

Replaces any standard outlet with ease, in as little as 10 minutes.

Features five adjustable light settings: Ultra Low, Low, Medium, High and OFF. Optional louver attachment also included for additional light level control.

Hidden sensor controls night light based on ambient light, automatically turning on when it is dark.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

### Specifications

#### General Info

Color	Black	UPC Number	785007032383
Country Of Origin	China	Product Line	Pass & Seymour
Application Sector	Residential	Type	Nightlight
Standard	cULus, UL Listed		

#### Dimensions

Product Width US	1.29 in	Product Height US	4.2 in
Product Depth US	1.3 in		

#### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

#### Technical Information

Voltage	125 V	Mounting Type	Box
Contact Configuration	15A	Contact Rating	125

---

Environmental Conditions

UL94 V2

Operating Cycles

50000

---