



radiant Collection
radiant® 15A Tamper-Resistant Outlet with Night Light
Part No. NTL885TRW



Perfect for adding a little light just where you need it, without sacrificing an outlet or dealing with unattractive plug-in models, this built-in night light from the radiant® Collection comes combined with a tamper-resistant outlet. A great upgrade for hallways and kids' bedrooms, it installs easily in place of a standard outlet and automatically comes on in the dark. With five adjustable light levels, you can easily set its brightness to meet your preferences or needs. Features the sleek, clean lines of radiant for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

Features five adjustable light settings: Ultra Low, Low, Medium, High and OFF. Optional louver attachment also included for additional light level control.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Replaces any standard outlet with ease, in as little as 10 minutes.

Hidden sensor controls night light based on ambient light, automatically turning on when it is dark.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007113723	Country Of Origin	China
Number of Receptacles	2	Features	Decorator Style, Nightlight
Outlet Type	Straight Blade, Tamper-Resistant	Application Sector	Hospitality, Residential
Wall Plate Included	No	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.29 in	Product Depth US	1.3 in
------------------	---------	------------------	--------

Product Height US	4.2 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Back and Side
---------------------	-----	---------------------	---------------

Number of Wires	3	Amperage	15 A
-----------------	---	----------	------

Number of Poles	Double Pole	Indoor/Outdoor	Indoor
-----------------	-------------	----------------	--------

Wire Connection Type	Internal Pressure Plates, Screw Terminals	Voltage	120.0 V, 125.0 V
----------------------	---	---------	------------------