



Nuvo
Discontinued - 8-in Nuvo Series Two Angled In-Ceiling Speakers
Part No. NV2IC8ANG



The NUVO Angled In-Ceiling speakers are designed to perform and look great. This 8" model has silk dome tweeters and poly woofers, and is finished beautifully with their completely rimless, magnetic grill. They also offer quick and secure installation by utilizing three dog legs, instead of the usual four, and includes pivoting tweeters. These tweeters are connected to a unique tweeter bridge that maximizes sound quality, looks great, and serves as a handle to hold the speaker by during installation. The NV-2IC8-ANG serves equally well for in-ceiling theater installation, as it does for targeted two channel audio installations. These speakers have a fifteen degree baffle that angles the woofer and tweeter towards the seating positions of the listener. Use these speakers to create an all in-ceiling, out-of-sight, home theater installation, or place them along a wall to make a targeted two channel listening environment.

Features & Benefits

| | |
|---|--|
| 8 ohm rated | Angled fifteen degree baffle with Pivoting tweeter |
| Grant better at home listening through quality design and materials | Magnetic rimless and paintable grill |
| Pivoting tweeter | Positions sound where you want it for use with home theater or two channel audio |
| Three dog leg design for easy installation | Unique tweeter bridge that also doubles as an installation handle |

Specifications

General Info

| | | | |
|--------------------|--------------|-------------------------|---------------------------|
| Product Line | Nuvo | Replaced by Part Number | NV2IC8 |
| UPC Number | 701963859055 | Country Of Origin | China |
| Application Sector | Residential | Standard | CE, RoHS, REACH Compliant |

Technical Information

| | | | |
|----------------------|----------|----------|---------|
| Transformer Settings | None | Wattage | 10.16 W |
| Impedance | 8.0 ohms | Decibels | 86 dB |