



Nuvo
Discontinued | P200 Player | Sub NVP100NA
 Part No. NVP200NA



With the P200 wireless player, give a room of your home instant access to endless music options, whether from your personal collection, the expansive libraries of Internet Radio, or even a Bluetooth-enabled device, always delivered in incredible fidelity. Check out the Player Portfolio mobile app. Outside North America? Use -EU, -UK or -AU when ordering.

Features & Benefits

- High-fidelity audio is delivered to every area of your home, and kept perfectly in sync. **Compatible with Legrand's other Nuvo Player Portfolio products for a truly custom, easily expandable system (up to sixteen zones).**
- Supports both wired ethernet and wireless 802.11n configuration options adding flexibility for any home. **Includes 802.11n wireless capability and utilizes both 2.4 and 5 Ghz bands, for fast signals and broad coverage.**
- All your favorite music is right at your fingertips with easy access to networked computers, streaming Internet Radio, and even audio content stored on any Android or iOS device. **Connect to storage devices, analog equipment, or home theater receivers through the unit's audio line-in, line-out, or USB ports.**
- Connect any Bluetooth device wirelessly, streaming audio from apps and services on your personal device throughout your system. **Manage your music via the convenient wall-mounted P10 keypad or wirelessly from the palm of your hand with free apps for your Apple or Android device.**
- Remote network and device management with Domotz PRO **Seamless integration into advanced automation systems from Vantage, Crestron, Control4, KNX, and more - visit the Player Portfolio third party drivers page . *Streaming services subject to geographic availability. Service subscriptions may be required.**

Specifications

General Info

UPC Number	701963853527	Country Of Origin	China
Product Line	Nuvo	Included	P200 Player, Power Cord, and Quick Start Guide
Application Sector	Residential	Standard	FCC, IC, CE-EMC, C-Tick, cTUVus, CE-LVD, RoHS

Additional Information

Product Environmental Profile Yes

Technical Information

Output Wattage	120 W	Wattage	31 W
----------------	-------	---------	------

Input	(1) TRS 3.5mm stereo jack (Line In), (1) TS 3.5mm stereo jack (Mic), (1) USB Type A, LAN (1) RJ44
-------	---
