



Ortronics  
Q-Series OFP Adapter Panel, 6-LC Quad , 24 fiber, single-mode Blue adapters, OS2  
Part No. OFP-LCQ24AC

Ortronics fiber adapter panel allows for flexibility and expansion with an industry accepted style. The adapter panel snaps in for installation and can be removed easily for future changes. The adapter panel is silkscreened for easy port identification



## Features & Benefits

Up to 72 LC fibers per RU	Available in, LC, SC, ST and blank styles
Made of durable polycarbonate	Zirconia ceramic sleeves for optimal performance
6, 8, 12 & 24 port panels	Color options available

## Specifications

### General Info

Product Line	Ortronics	UPC Number	662875593812
Country Of Origin	Mexico	Type	Adapter

### Dimensions

Product Width US	5.12 in	Product Depth US	1.15 in
Product Height US	1.19 in		

### Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

### Technical Information

Ferrule	Zirconia Ceramic	Number of Fibers	24 Fibers
Fiber Type	OM3/4	Form Factor	LC Quad