




Cablofil
09-7400-0010-06 FG 4"H Fiberglass Ladder 10'L 06"W
Part No. P027686



For extremely corrosive applications we offer a full line of straight sections, fittings, covers and mounting accessories in polyester and vinylester fiberglass. Rail heights are available in 4" and 6" and widths are available up to 36".

Features & Benefits

Material: Pultruded from Glass Fiber Reinforced Fire Retardant Polyester Resin

Finish: Plain

Bottom: Ldr = 1" square tube rung

Tray Design: Tray construction and markings

Connectors: Supplied in pairs with hardware

Specifications

General Info

Product Line	Cablofil	Finish	Other
UPC Number	800388511606	Country Of Origin	United States
Bottom Type	Ladder	Application Sector	Commercial, Industrial
Type	Straight Sections		

Dimensions

Product Width US	6.0 in	Product Weight US	18.281 lb
Product Volume US	1.667 cu ft	Product Depth US	120.0 in
Product Height US	4.0 in	Rung Spacing	9 in

Trade Programs

BAA	Yes
-----	-----

Technical Information

NEMA Load Class	12C
-----------------	-----