



Range and Dryer Box with captive Mounting Nails on Each End. 1/2-inch offset for wood or steel stud mounting with metal cable clamp. 12 pack.

Features & Benefits

Auto/Clamps on each end eliminate the need for separate cable clamps.

Easy installation, rectangular cutout.

Location ribs enable the installer to quickly and accurately maintain a 1/2 inch offset.

Constructed of impact-resistant thermoplastic.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007306156	Country Of Origin	United States
Features	Integral Clamp	Installation Location	Wall
Application Sector	Commercial, Residential	Standard	UL listed
Warranty Type	1-Year Limited Warranty	Type	Range & dryer Box

Dimensions

Product Width US	4.0 in	Product Depth US	4.0 in
Product Length US	3.75 in	Cubic Capacity	42 in ³

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Number of Gangs	1	Indoor/Outdoor	Indoor
Cable Entry	Side	Box Shape	Rectangular
Mounting Type	Nail On		
