



Cablofil

VC-4A12B-S144-18 AL 4H VENTCOR 144L 18W
Part No. P300068



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

Features & Benefits

Material: Aluminum Alloy 6063-T6

Finish: Plain

Bottom: Ldr: 1" wide I rung SB: Flat Sheet over 12" Rung Spacing. SC: Solid Corrugated VC: Vented Corrugated

Construction: Welded

Tray Design: Tray construction and markings are per the latest edition of NEMA Standards Publication VE1, CSA C22.2 No. 126.

Tray Grounding Capability: Classified as an equipment grounding conductor per NEC 392.60.

Specifications

General Info

UPC Number	800388059337	Country Of Origin	Mexico
Product Line	Cablofil	Finish	Aluminum

Dimensions

Product Volume US	6.711 cu ft	Product Width US	19.5 in
Product Height US	4.13 in	Product Weight US	25.105 lb
Product Depth US	144.0 in		

Buy American Act Compliance

BAA	Yes
-----	-----