



Cablofil

SC-4A12B-S120-12 AL 4H SOLCOR 120L 12W
Part No. P300074



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

Features & Benefits

Material: Aluminum Alloy 6063-T6

Finish: Plain

Bottom: Ldr: 1" wide I rung SB: Flat Sheet over 12" Rung Spacing. SC:Solid Corrugated VC: Vented Corrugated

Construction: Welded

Tray Design: Tray construction and markings are per the latest edition of NEMA Standards Publication VE1, CSA C22.2 No. 126.

Tray Grounding Capability: Classified as an equipment grounding conductor per NEC 392.60.

Specifications

General Info

| | | | |
|--------------|--------------|-------------------|----------|
| UPC Number | 800388059399 | Country Of Origin | Mexico |
| Product Line | Cablofil | Finish | Aluminum |

Dimensions

| | | | |
|-------------------|-------------|-------------------|-----------|
| Product Volume US | 3.872 cu ft | Product Width US | 13.5 in |
| Product Height US | 4.13 in | Product Weight US | 18.097 lb |
| Product Depth US | 120.0 in | | |

Buy American Act Compliance

| | |
|-----|-----|
| BAA | Yes |
|-----|-----|