



Cablofil
SB-4A12B-S120-30 AL 4H SOLBOT 120L 30W
Part No. P300091



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

Features & Benefits

Material: Aluminum Alloy 6063-T6

Finish: Plain

Bottom: Ldr: 1" wide I rung SB: Flat Sheet over 12" Rung Spacing.
SC:Solid Corrugated VC: Vented Corrugated

Construction: Welded

Tray Design: Tray construction and markings are per the latest edition of NEMA Standards Publication VE1, CSA C22.2 No. 126.

Tray Grounding Capability: Classified as an equipment grounding conductor per NEC 392.60.

Specifications

General Info

Product Line	Cablofil	Finish	Aluminum
UPC Number	800388059566	Country Of Origin	Mexico
Bottom Type	Solid Bottom	Application Sector	Commercial, Industrial
Type	Straight Sections		

Dimensions

Product Width US	31.5 in	Product Weight US	34.345 lb
Product Volume US	9.034 cu ft	Product Depth US	120.0 in
Product Height US	4.13 in		

Trade Programs

BAA	Yes
-----	-----

Technical Information

NEMA Load Class	12B
-----------------	-----