

Cablofil VC-4A12C-S144-24 AL 4H VENTCOR 144L 24W

Part No. P300195



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding, Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

Features & Benefits

Material: Aluminum Alloy 6063-T6 Finish: Plain

Bottom: Ldr: 1" wide I rung SB: Flat Sheet over 12" Rung Spacing. Construction: Welded

SC:Solid Corrugated VC: Vented Corrugated

Tray Design: Tray construction and markings are per the latest edition

of NEMA Standards Publication VE1, CSA C22.2 No. 126.

Tray Grounding Capability: Classified as an equipment grounding conductor per NEC 392.60.

Specifications

General Info			
Product Line	Cablofil	Finish	AL
UPC Number	800388060609	Country Of Origin	Mexico
Dimensions			
Product Width US	25.5 in	Product Weight US	31.232 lb
Product Volume US	8.798 cu ft	Product Depth US	144.0 in
Product Height US	4.14 in		
Buy American Act Compliance			
BAA	Yes		