



Cablofil  
SB-4A12C-S120-24 AL 4H SOLBOT 120L 24W  
Part No. P300230



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

## Features & Benefits

Material: Aluminum Alloy 6063-T6

Finish: Plain

Bottom: Ldr: 1" wide I rung SB: Flat Sheet over 12" Rung Spacing.  
SC:Solid Corrugated VC: Vented Corrugated

Construction: Welded

Tray Design: Tray construction and markings are per the latest edition of NEMA Standards Publication VE1, CSA C22.2 No. 126.

Tray Grounding Capability: Classified as an equipment grounding conductor per NEC 392.60.

## Specifications

### General Info

Product Line	Cablofil	Finish	Aluminum
UPC Number	800388060951	Country Of Origin	Mexico
Bottom Type	Solid Bottom	Application Sector	Commercial, Industrial
Type	Straight Sections		

### Dimensions

Product Width US	25.5 in	Product Weight US	29.461 lb
Product Volume US	7.331 cu ft	Product Depth US	120.0 in
Product Height US	4.14 in		

## Trade Programs

BAA	Yes
-----	-----

Technical Information

NEMA Load Class	12C
-----------------	-----