




Cablofil
LD-4A-90VI12-06 AL 4H 90° IVR 12R 06W (TRA)
Part No. P302831



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

Features & Benefits

Includes splices and hardware

Specifications

General Info

Product Line	Cablofil	Finish	Aluminum
UPC Number	800388086975	Country Of Origin	Mexico
Bottom Type	Ladder	Application Sector	Commercial, Industrial
Type	Vertical Elbows		

Dimensions

Product Width US	7.5 in	Product Weight US	6.356 lb
Product Volume US	1.567 cu ft	Product Depth US	19.0 in
Product Height US	19.0 in	Radius	12 in

Trade Programs

BAA	Yes
-----	-----