



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

Features & Benefits

Material: Aluminum Alloy 5052 - H32

Finish: Plain

Height (H): Tray height: 4", 5", 6", 7" (less 1/2")

RN (tray width reduction): 3", 6", 9", 12", 15", 18", 21", 24", 27", 30"

Torque: 19 - 25 ft-lbs

Specifications

General Info

Product Line	Cablofil	Finish	Aluminum
UPC Number	800388200890	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Type	Splicing

Dimensions

Product Width US	10.75 in	Product Weight US	2.036 lb
Product Volume US	0.16 cu ft	Product Depth US	6.625 in
Product Height US	3.875 in		

Trade Programs

BAA	Yes
-----	-----