



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

Features & Benefits

Made from 12-gauge strut

Hangers have 9/16" diameter holes 13/16" from each end to accept 1/2" threaded rod

When used with Z-type hold-down clamps, select hanger with flange out dimensions

Specifications

General Info

| | | | |
|--------------------|------------------------|--------|---------------|
| Product Line | Cablofil | Finish | Stainless 316 |
| Application Sector | Commercial, Industrial | Type | Accessories |

Dimensions

| | |
|-------------------|----------|
| Product Weight US | 3.516 lb |
|-------------------|----------|