



Cablofil
SB-6A-90VO12-24 AL 6H 90 OVR 12R 24W
Part No. P642910



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

Features & Benefits

Includes splices and hardware

Specifications

General Info

Product Line	Cablofil	Finish	Aluminum
UPC Number	800388169319	Country Of Origin	Mexico
Bottom Type	Solid Bottom	Application Sector	Commercial, Industrial
Type	Vertical Elbows		

Dimensions

Product Width US	25.5 in	Product Weight US	10.907 lb
Product Volume US	6.508 cu ft	Product Depth US	21.0 in
Product Height US	21.0 in	Radius	12 in

Trade Programs

BAA	Yes
-----	-----