



Wiremold Discontinued - PB Series 160kA SPD for sub-panel apps/Rated 120/240V Split-phase Part No. PB120T



For surge protection at the sub panel or near sensitive equipment. Designed for residential and light commercial/industrial applications. Dimensions: 6 5/16" x 4 3/4" x 3 9/16" (160mm x 120mm x 90mm). Ten-year, unconditional product warranty. Electrical Service: 120/240V, Single 0 3-Wire and Ground. Surge Protection: 160kA. NOTE: Add suffix ""-A"" to part number for NO/NC dry contact relay for connecting remote monitoring device. Add suffix ""-B"" to part number for EMI/RFI noise filter. Add ""-AB"" to part number for both options.

Features & Benefits

For surge protection at the sub panel or near sensitive equipment. Designed for residential and light commercial/industrial applications.

Dimensions: 6 5/16" x 4 3/4" x 3 9/16" (160mm x 120mm x 90mm). Electrical Service: 120/240V, Single 0 3-Wire and Ground. Surge Protection: 160kA.

Ten-year, unconditional product warranty.

NOTE: Add suffix "-A" to part number for NO/NC dry contact relay for connecting remote monitoring device. Add suffix "-B" to part number for EMI/RFI noise filter. Add "-AB" to part number for both options.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776005851
Country Of Origin	United States	Application Sector	Commercial
Standard	cETLus Listed: Guide VZCA	Type	Current Monitoring

Dimensions

Product Weight US	0.77 lb
-------------------	---------

Listing Agencies / 3rd Party Agencies

ETL Listed	Yes
------------	-----

Trade Programs

USMCA	Yes
-------	-----

Additional Information

RoHS Compliant	Yes		
Technical Information			
Phase	Single	Connection	Hard-wired
Class	75	Short Circuit Rating	160kA
Type of Indicators	Light	Voltage	120.0 V
Environmental Conditions	Indoor		