



Ortronics  
**Discontinued Clarity 10G 24-port panel - Cat6a - six-port modules - 19 in x 1.75 in**  
Part No. PHD610U24

Clarity 10G 24-port high density patch panel with multiport modules (6 jacks in a group). The Clarity 10G panel maximizes innovative methods for circuit isolation and supports the alien crosstalk of IEEE 10G and TIA Category 6 cabling specifications. It occupies one rack unit and measures 19" x 1.75".



## Features & Benefits

- Recessed design with lower mounted profile: Directs cords more easily to vertical management.
- Center tuned to Clarity 10G patch cords: More transparent mated union resulting in superior performance.
- 10 Gig compatible IDC towers: Designed to accept larger 10G cable conductors.
- High density design: Maximizes rack utilization.
- ETL channel tested to TIA T568B.2-10 (draft 5 Augmented Category 6) & characterized out 500MHz: Ensures component performance.
- Universally wired 110 termination: Supports T568A and T568B installs.
- Supplied rear cable management: Supports good cabling practices.
- RoHS compliant: Lead free.

## Specifications

### General Info

Product Line	Ortronics	Replaced by Part Number	PHD6AU24
Color	Black	UPC Number	662875611226
Country Of Origin	Mexico	Application Sector	Commercial/Industrial
Type	Panel		

### Dimensions

Product Width US	19.0 in	Product Height US	1.75 in
------------------	---------	-------------------	---------

### Additional Information

RoHS Conformant	Yes	Product Has Potential to Contribute to LEED	Yes
-----------------	-----	---	-----

---

Product Environmental Profile      Yes

---