



Ortronics
CLARITY CAT6A 48 PORT FLAT PANEL, 110/6PORT, T568A/B, 2RU, White
Part No. PHD6AU48-W



Clarity® 6A patch panels are available in the traditional multi-port panel format with 6-port modules and the added flexibility of flat or angled versions. Large termination bay allows for high visibility and more space for wiring during terminations. Includes rear wire manager.

Features & Benefits

- More transparent signal path with Clarity 6A cords
- Standard termination practice – 110 tool
- IDC towers designed to accept larger 6A/10 Gig cable conductors
- Easy-to-follow universal wiring label is quick and user-friendly to eliminate confusion
- Panels include label fields and rear cable management
- Meets TIA 568C.2 Category 6A component specifications
- Backwards compatible to Category 6 and Category 5e

Specifications

General Info

Product Line	Ortronics	Color	White
UPC Number	662875730262	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Warranty Type	5-Year
Type	Panel		

Dimensions

Product Width US	19.0 in	Product Depth US	4.5 in
Product Height US	3.5 in		

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Compatibility	HDJ	Rack Units	2
Wire Gauge	22 AWG	Number of Ports	48
Shielded/Unshielded	Shielded	Connector Type	RJ-45
Wattage	100 W	Voltage	60.0 V