



Pass and Seymour  
Discontinued - Light Duty, Short Length, Flexible Eye  
Part No. PL0621

Light Duty, Short Length, Flexible Eye. Cable Diameter - 0.620-0.740", Mesh Length - 11", Break Strength - 4,100 lbs.



## Features & Benefits

Light-Duty grips are the most economical pulling grips for many applications, such as industrial plant wiring, and rewiring, and underground electrical pulls.

Mesh  
Length: 11

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Various Types of Pulling, Support and Strain Relief Grips	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

### Technical Information

Maximum Cable Range	0.62 in	Minimum Cable Range	0.74 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Approx. Break Strength: 4100		