



Pass and Seymour
Light Duty, Short Length, Flexible Eye
Part No. PL0621

Light Duty, Short Length, Flexible Eye. Cable Diameter - 0.620-0.740-inch, Mesh Length - 11-inch, Break Strength - 4,100 lbs.



Features & Benefits

Light-Duty grips are the most economical pulling grips for many applications, such as industrial plant wiring, and rewiring, and underground electrical pulls.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007992793
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

Technical Information

Capacity	Various Cable Diameter Ranges	Cable Size	Cable Dia. Range: 0.620-0.740: Mesh Length: 11
Mounting	Consult the Factory for Mounting Recommendations	Load	Approx. Break Strength: 4,100