



Series 18 In Line Connectors - five female

Features & Benefits

Interchangeable with Canadian CAM devices from other manufacturers. Ball nose design achieves NEMA 3R, 4 rating. Designed specifically for Sea Way cable. Accepts #6 through 4/0 size wire.

Double set screws for premium wire retention. Locking screw prevents contact from rotating inside housing.

Specifications

General Info

| | | | |
|--------------------|------------------------|-------------------|-----------------|
| Product Line | Pass & Seymour | Color | Blue |
| UPC Number | 785007255256 | Country Of Origin | Mexico |
| Application Sector | Commercial, Industrial | Standard | UL, cUL, cCSAus |

Dimensions

| | |
|-------------------|--------|
| Product Length US | 6.8 in |
|-------------------|--------|

Technical Information

| | | | |
|-----------|-----------|-----------------|-------------|
| Amperage | 400 A | Number of Poles | Single Pole |
| Wire Size | 6 - 2 AWG | Voltage | 600.0 V |

| | |
|--------------------------|---|
| Environmental Conditions | Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4 |
|--------------------------|---|