



Series 18 In Line Connectors - Male

Features & Benefits

Interchangeable with Canadian CAM devices from other manufacturers. Ball nose design achieves NEMA 3R, 4 rating. Designed specifically for Sea Way cable. Accepts #6 through 4/0 size wire. Double set screws for premium wire retention. Locking screw prevents contact from rotating inside housing.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Application Sector	Commercial/Industrial
Standard	UL, cUL, cCSAus		

Dimensions

Product Length US	6.875 in
-------------------	----------

Technical Information

Amperage	400 A	Number of Poles	Single Pole
Wire Size	6 - 2 AWG	Voltage	600.0 V
Environmental Conditions	Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact; Flammability UL94 V2; Enclosure: NEMA Type 3R and 4		