



Series 18 In Line Connectors - Male

## Features & Benefits

Interchangeable with Canadian CAM devices from other manufacturers. Ball nose design achieves NEMA 3R, 4 rating. Designed specifically for Sea Way cable. Accepts #6 through 4/0 size wire.

Double set screws for premium wire retention. Locking screw prevents contact from rotating inside housing.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Green
UPC Number	785007255270	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Standard	UL, cUL, cCSAus

### Dimensions

Product Length US	6.875 in
-------------------	----------

### Technical Information

Amperage	400 A	Number of Poles	Single Pole
Wire Size	6 - 2 AWG	Voltage	600.0 V
Environmental Conditions	Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4		