



Series 18 In Line Connectors - Male

## Features & Benefits

Interchangeable with Canadian CAM devices from other manufacturers. Ball nose design achieves NEMA 3R, 4 rating. Designed specifically for Sea Way cable. Accepts #6 through 4/0 size wire.

Double set screws for premium wire retention. Locking screw prevents contact from rotating inside housing.

## Specifications

### General Info

|                    |                        |                   |                 |
|--------------------|------------------------|-------------------|-----------------|
| Product Line       | Pass & Seymour         | Color             | Blue            |
| UPC Number         | 785007255355           | Country Of Origin | Mexico          |
| Application Sector | Commercial, Industrial | Standard          | UL, cUL, cCSAus |

### Dimensions

|                   |          |
|-------------------|----------|
| Product Length US | 6.875 in |
|-------------------|----------|

### Technical Information

|                          |   |                 |             |
|--------------------------|---|-----------------|-------------|
| Amperage                 | 400 A   | Number of Poles | Single Pole |
| Wire Size                | 4/0   | Voltage         | 600.0 V     |
| Environmental Conditions | Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact:<br>Flammability UL94 V2: Enclosure: NEMA Type 3R and 4 |                 |             |