



Series 18 In Line Connectors - Male

Features & Benefits

Interchangeable with Canadian CAM devices from other manufacturers. Ball nose design achieves NEMA 3R, 4 rating. Designed specifically for Sea Way cable. Accepts #6 through 4/0 size wire. Double set screws for premium wire retention. Locking screw prevents contact from rotating inside housing.

Specifications

General Info

| | | | |
|-------------------|-----------------|--------------------|-----------------------|
| Product Line | Pass & Seymour | Color | Blue |
| Country Of Origin | Mexico | Application Sector | Commercial/Industrial |
| Standard | UL, cUL, cCSAus | | |

Dimensions

| | |
|-------------------|----------|
| Product Length US | 6.875 in |
|-------------------|----------|

Technical Information

| | | | |
|-----------|-------|-----------------|-------------|
| Amperage | 400 A | Number of Poles | Single Pole |
| Wire Size | 4/0 | Voltage | 600 V |

| | |
|--------------------------|--|
| Environmental Conditions | Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4 |
|--------------------------|--|