



New requirements for reducing energy consumption in commercial buildings are here. With devices that are so easy to understand, install and use, our full line of P&S Plug Load Controllable solutions will take a load off your mind and a load off your customers' electric bills.

Features & Benefits

Specifications

General Info

Color	Black
UPC Number	785007040036
Countries Of Origin	China
Product Line	Pass & Seymour
Application Sector	Commercial
Standard	RoHS, CSA Listed, CuIUS, UL Listed, FSUL

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Poles	Double Pole
Voltage	125 V
Connection	Screw terminals
Dielectric Strength	Withstands 2000V minimum
Phase	Single
Temperature Rating	Maximum continuous +60°C, minimum -40° without impact

Wire Size #14 -#10 AWG Copper Conductor Only

Number of Wires 3

Environmental Conditions UL94 V2
