



Pass and Seymour  
15A, 125V Heavy Duty Spec Grade Plug Load Timer Receptacle, Light Almond  
Part No. PLT26251LA



New requirements for reducing energy consumption in commercial buildings are here. With devices that are so easy to understand, install and use, our full line of Pass and Seymour Plug Load Controllable solutions will take a load off your mind and a load off your customers electric bills.

## Features & Benefits

Wire Size: #14 - #10 AWG Copper Conductor Only

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Light Almond
Country Of Origin	China	Application Sector	Commercial
Standard	RoHS, CSA Listed, CulUS, UL Listed, FSUL		

### Dimensions

Product Width US	1.73 in	Product Depth US	1.25 in
Product Height US	2.68 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Dielectric Strength	Withstands 2000V minimum	Phase	Single
Connection	Screw terminals	Number of Wires	3

Temperature Rating	-40° - 60° C	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Voltage	125 V	Environmental Conditions	UL94 V2