



Medium Duty, Flexible Eye. Cable Diameter - 0.370-0.490", Mesh Length - 13" , Break Strength - 2,600 lbs.

Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Specifications

General Info

UPC Number	785007993530	Country Of Origin	Mexico
Product Line	Pass & Seymour	Application Sector	Industrial
Construction	Various Types of Pulling, Support and Strain Relief Grips	Standard	UL/CSA Approval (consult factory)

Technical Information

Mounting	Consult the Factory for Mounting Recommendations	Cable Size	Cable Dia. Range: 0.370-0.490: Mesh Length: 13
Capacity	Various Cable Diameter Ranges	Load	Approx. Break Strength: 2,600