



Medium duty, Flexible eye. Cable Diameter - 0.500-0.740-inch, Mesh Length - 17-inch, Break Strength - 3,400 lbs.

Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007993547
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

Technical Information

Capacity	Various Cable Diameter Ranges	Cable Size	Cable Dia. Range: 0.500-0.740: Mesh Length: 17
Mounting	Consult the Factory for Mounting Recommendations	Load	Approx. Break Strength: 3,400