



**Pass and Seymour**  
**Medium Duty, Standard Length, Flexible Eye, T-Type**  
Part No. PM0752



Medium Duty, Standard Length, Flexible Eye, T-Type. Cable Diameter - 0.750-0.990", Mesh Length - 36", Eye Diameter - 1/4", Break Strength - 6,800 lbs.

## Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

## Specifications

### General Info

UPC Number	785007185508	Country Of Origin	Mexico
Product Line	Pass & Seymour	Application Sector	Industrial
Construction	Various Types of Pulling, Support and Strain Relief Grips	Standard	UL/CSA Approval (consult factory)

### Technical Information

Mounting	Consult the Factory for Mounting Recommendations	Cable Size	Cable Dia. Range: 0.750-0.990: Mesh Length: 36: Eye Diameter: 1/4
Capacity	Various Cable Diameter Ranges	Load	Approx. Break Strength: 6,800