

Medium duty, Flexible eye. Cable Diameter - 1.00-1.240-inch, Mesh Length - 28-inch, Break Strength - 8,100 lbs.



Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007993561
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

Technical Information

Capacity	Various Cable Diameter Ranges	Cable Size	Cable Dia. Range: 1.000-1.240: Mesh Length: 28
Mounting	Consult the Factory for Mounting Recommendations	Load	Approx. Break Strength: 8,100